



Locking Devices, Bryant Midget Locking, Industrial, Flanged Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, ML-2R, Screw Terminal, Black & White

By Bryant
Catalog # 7596ER

Locking Devices, Bryant Midget Locking, Industrial, Flanged Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, ML-2R, Screw Terminal, Black & White

Features

- Industrial
- Flanged Receptacle
- 15A 125V
- 2-Pole 3-Wire Grounding
- ML-2R

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	ML-2R

Conductor

Number Of Wires	3-Wire
Wire Size	#18 AWG to #12 AWG
Number Of Poles	2-Pole

Current

Amperage Rating	15 A
Voltage Rating Description	125V
Current/Amperage Rating Description	15 Amp
Current Rating	15 A



Voltage Rating	125 V
Connectivity	Terminal Screws
Phase	Single Phase

Dimensions

Length	2.06 in
Display Size	Midget Locking
Height	1.17 in
Width	1.62 in
Dimensions	2.06 in x 1.62 in x 1.17 in

General

Color	White
Style	Grounding
OEM Brand Name	Hubbell Bryant
UPC	781786671454
Type	Flanged Receptacle
Material - Mounting Hardware	Screw Mounting
Item Type	15A Midget Flanged Receptacle
Material	Composite

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)