



Straight Blade Devices, Receptacles, Single, Hospital Grade, 15A 125V, 2-Pole 3-Wire Grounding, Back and Side Wired, 5-15R, Orange, Single Pack

By Bryant
Catalog # 8210IG

Straight Blade Devices, Receptacles, Single, Hospital Grade, 15A 125V, 2-Pole 3-Wire Grounding, Back and Side Wired, 5-15R, Orange, Single Pack

Features

- Single
- Hospital Grade
- 15A 125V
- 2-Pole 3-Wire Grounding
- Back and Side Wired

Application

Hospital Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Nema Rating	5-15R

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

Current

Amperage Rating	15 A
Voltage Rating Description	125 V
Current Rating	15 A
Voltage Rating	125 V
Wattage	1875 W
Connectivity	Back and Side Wired
Phase	Single Phase



Current / Amperage Rating	15 A
---------------------------	------

Dimensions

Length	3.28 in
Display Size	Standard Sized Product
Weight	0.1 lb.
Height	0.91 in
Width	1.38 in
Dimensions	3.28 in x 1.38 in x 0.91 in

General

Color	Orange
Style	Finder Groove Face
Series	Hospital Grade
OEM Brand Name	Hubbell Bryant
UPC	781786731349
Type	Single Receptacle
Material - Mounting Hardware	Screw Mounting
Item Type	Single
Material	Composite

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)