



Straight Blade Devices, Receptacles, Single, Hospital Grade, 20A 250V, 2-Pole 3-Wire Grounding, Back and Side Wired, 6-20R, Orange, Single Pack

By Bryant  
Catalog # 8410IG

Straight Blade Devices, Receptacles, Single, Hospital Grade, 20A 250V, 2-Pole 3-Wire Grounding, Back and Side Wired, 6-20R, Orange, Single Pack

Features

- Single
- Hospital Grade
- 20A 250V
- 2-Pole 3-Wire Grounding
- Back and Side Wired

Application

Hospital Grade

Specifications

|                          |                                                 |
|--------------------------|-------------------------------------------------|
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| EU RoHS Indicator        | No                                              |
| Nema Rating              | 6-20R                                           |

Conductor

|                 |                    |
|-----------------|--------------------|
| Number Of Wires | 3-Wire             |
| Wire Size       | #14 AWG to #12 AWG |
| Number Of Poles | 2-Pole             |

Current

|                            |                     |
|----------------------------|---------------------|
| Current Rating             | 20 A                |
| Amperage Rating            | 20 A                |
| Voltage Rating Description | 250 V               |
| Phase                      | Single Phase        |
| Current / Amperage Rating  | 20 A                |
| Connectivity               | Back and Side Wired |
| Wattage                    | 5000                |



|                |                             |
|----------------|-----------------------------|
| Voltage Rating | 250 V                       |
| Dimensions     |                             |
| Display Size   | Standard Sized Product      |
| Length         | 3.28 in                     |
| Width          | 1.38 in                     |
| Weight         | 0.15 lb.                    |
| Height         | 0.91 in                     |
| Dimensions     | 3.28 in x 1.38 in x 0.91 in |

General

|                              |                    |
|------------------------------|--------------------|
| Series                       | Hospital Grade     |
| OEM Brand Name               | Hubbell Bryant     |
| Style                        | Finder Groove Face |
| Color                        | Orange             |
| Item Type                    | Single             |
| Material - Mounting Hardware | Screw Mounting     |
| Type                         | Single Receptacle  |
| Material                     | Composite          |
| UPC                          | 781786731431       |

Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)