



Straight Blade Devices, Receptacles, Flush Mount Single, Industrial Grade, 50A 3-Phase 250V AC, 3-Pole 4-Wire Grounding, 15-50R, Black, Single Pack

By Bryant
Catalog # 8450FR

Straight Blade Devices, Receptacles, Flush Mount Single, Industrial Grade, 50A 3-Phase 250V AC, 3-Pole 4-Wire Grounding, 15-50R, Black, Single Pack

Features

- Flush Mount Single
- Industrial Grade
- 50A 3-Phase 250V AC
- 3-Pole 4-Wire Grounding
- 15-50R

Application

Industrial Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Nema Rating	15-50R
Industry Standard(s)	WR Rating

Conductor

Number Of Wires	4-Wire Grounding
Wire Size	#10 AWG to #6 AWG
Number Of Poles	3-Pole

Current

Amperage Rating	50 A
Voltage Rating Description	250V kV
Current Rating	50 A



Voltage Rating	250V kV
Wattage	12500
Connectivity	Pressure Terminal Screws
Phase	Three Phase
Current / Amperage Rating	50 A

Dimensions

Display Size	Standard Sized Product
Weight	0.65 lb.

General

Color	Black
OEM Brand Name	Hubbell Bryant
UPC	781786674103
Material - Mounting Hardware	Screw Mounting
Item Type	Single
Material	Composite

Logistics

Pallet Quantity	1200
Carton Quantity	10

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)