



Straight Blade Devices, Male Plug, Heavy Duty, Industrial/Commercial IGrade, Straight, 60A 3 Phase 250V AC, 3-Pole 4-Wire Grounding, 15-60P

By Bryant
Catalog # 8460NP

Straight Blade Devices, Male Plug, Heavy Duty, Industrial/Commercial IGrade, Straight, 60A 3 Phase 250V AC, 3-Pole 4- Wire Grounding, 15-60P, Black, Single Pack

Features

- Heavy Duty
- Industrial/Commercial IGrade
- Straight
- 60A 3 Phase 250V AC
- 3-Pole 4- Wire Grounding

Application

Heavy Duty

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Nema Rating	15-60P

Conductor

Number Of Wires	4-Wire
Wire Size	#6 AWG to #4 AWG
Number Of Poles	3-Pole

Configuration

Cord Type	All Portable
-----------	--------------

Current

Current Rating	60 A
Amperage Rating	60 A
Voltage Rating Description	3 Phase 250 VAC

Phase	Three Phase
Current / Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Wattage	12480
Voltage Rating	Three Phase 250 VAC

Dimensions

Display Size	Standard Sized
Length	2.88 in
Width	4.13 in
Weight	0.75 lb.

General

Series	Industrial
OEM Brand Name	Hubbell Bryant
Style	Extra Heavy Duty
Color	Black
Item Type	Standard
Material - Mounting Hardware	Cord Mounted
Type	Plug
Material	Composite
UPC	781786731486

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
[Catalog Page \[English\]](#)