



Switches and Lighting Controls, Industrial Grade, Toggle Switches, Manual Motor Controller Accessories, Three Pole, 85A 600V AC, Side Wired Only

By Bryant
Catalog # 85003D



Switches and Lighting Controls, Industrial Grade, Toggle Switches, Manual Motor Controller Accessories, Three Pole, 85A 600V AC, Side Wired Only, Black

Features

- Toggle
- Manual Motor Controller Three Pole
- 85A 600V AC
- Side Wired Only

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes

Conductor

Number Of Poles	3 Pole
-----------------	--------

Current

Phase	Three Phase
Current / Amperage Rating	85 A
Connectivity	Pressure Terminal Screws
Current Rating	85 A
Amperage Rating	85 A
Voltage Rating Description	600V AC kV
Wattage	51000
Voltage Rating	600V AC kV

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Force Related

Load Capacity	Inductive
---------------	-----------

General

Item Type	Open Switch
Material - Mounting Hardware	Screw Mounting
Type	Back Wire
Series	Standard Toggle
OEM Brand Name	Hubbell Bryant
UPC	781786631939
Style	Motor Controller/Disconnect

Logistics

Carton Quantity	10
-----------------	----

Operational

Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Minimum Continuous -40 Deg C without Impact

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)