



Locking Devices, Flanged Receptacle, 20A 250V, 2- Pole 2-Wire Non-Grounding, Non-NEMA, Black

By Bryant
Catalog # 8809ER

Locking Devices, Flanged Receptacle, 20A 250V, 2- Pole 2-Wire Non-Grounding, Non-NEMA, Black

Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws
- Mounting screws included

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Standards - RoHS Compliance Status	CM
Nema Rating	L2-20R

Conductor

Number Of Wires	2-Wire
Wire Size	#14 AWG to #8 AWG
Number Of Poles	2-Pole

Current

Current/Amperage Rating	20 Amp
Description	
Current Rating	20 A
Amperage Rating	20 A



Voltage Rating Description	250V
Phase	Single Phase
Connectivity	Terminal Screws
Voltage Rating	250 V

Dimensions

Display Size	Standard Sized Product
Length	2.56 in
Width	2.56 in
Height	1.72 in
Dimensions	2.56 in x 2.56 in x 1.72 in

General

OEM Brand Name	Hubbell Bryant
Style	Equipment Base
Color	White
Item Type	20A Flanged Receptacle
Material - Mounting Hardware	Screw Mounting
Type	Flanged Receptacle
Material	Composite
UPC	781786630796

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)