



Straight Blade Devices, Receptacles, Duplex, Decorator Hospital Grade, Isolated Ground, Back and Side Wired, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R

By Bryant
Catalog # 9200IGI

Straight Blade Devices, Receptacles, Duplex, Decorator Hospital Grade, Isolated Ground, Back and Side Wired, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Ivory, Single Pack



Features

- Duplex
- Decorator Hospital Grade
- Isolated Ground
- Back and Side Wired
- 15A 125V

Application

Hospital Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	5-15R

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

Current

Current Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	125 V
Phase	Single Phase
Current / Amperage Rating	15 A
Connectivity	Back and Side Wired
Wattage	1875

Voltage Rating	125 V
Dimensions	
Display Size	Standard Sized Product
Length	3.28 in
Width	1.36 in
Weight	0.2 lb.
Height	1.03 in
Dimensions	3.28 in x 1.36 in x 1.03 in

General

Series	Straight Blade
OEM Brand Name	Hubbell Bryant
Style	Decorator
Color	Ivory
Item Type	Decorator Duplex
Material - Mounting Hardware	Screw Mounting
Type	Single Receptacle
Material	Composite
UPC	781786741607

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Installation Manual \[French, English\]](#)