



# Straight Blade Devices, Receptacles, Duplex, Decorator Commercial/Industrial Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5- 15R, Back and Side Wired

By Bryant  
Catalog # 9252GRY



Straight Blade Devices, Receptacles, Duplex, Decorator  
Commercial/Industrial Grade, 15A 125V, 2-Pole 3-Wire  
Grounding, 5-15R, Back and Side Wired, Gray, Single Pack

## Features

- Duplex
- Decorator Commercial/Industrial Grade
- 15A 125V
- 2-Pole 3-Wire Grounding
- 5-15R

## Application

Specification Specification Grade

## General

Catalog Number	9252GRY
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Decorator Duplex
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Series	Heavy Duty
Style	Decorator
Type	Duplex Receptacle
UPC	781786741966

## Dimensions

Dimensions	3.28 in x 1.36 in x 1.03 in
Display Size	Standard Sized Product
Height	1.03 in
Length	3.28 in

Weight	0.2 lb
Width	1.36 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired Terminal Screws
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

## Certifications And Compliance

Nema Rating	5-15R
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - 9252GRY Specification Sheet English](#)  
[Specifications - 9252GRY Specification Sheet French](#)