



## Straight Blade Devices, Receptacles, Duplex, Decorator Commercial/Industrial Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Back and Side Wired

By Bryant  
Catalog # [9252I](#)

Straight Blade Devices, Receptacles, Duplex, Decorator Commercial/Industrial Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Back and Side Wired, Ivory, Single Pack



### Features

- Duplex
- Decorator Commercial/Industrial Grade
- 15A 125V
- 2-Pole 3-Wire Grounding
- 5-15R

### Application

Specification Specification Grade

### Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	5-15R

### Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

### Current

Current Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	125 V
Phase	Single Phase
Current / Amperage Rating	15 A
Connectivity	Back and Side Wired Terminal Screws

Wattage	1875
Voltage Rating	125 V

### Dimensions

Display Size	Standard Sized Product
Length	3.28 in
Width	1.36 in
Weight	0.05 lb.
Height	1.03 in
Dimensions	3.28 in x 1.36 in x 1.03 in

### General

Series	Heavy Duty
OEM Brand Name	Hubbell Bryant
Style	Decorator
Color	Ivory
Item Type	Decorator Duplex
Material - Mounting Hardware	Screw Mounting
Type	Duplex Receptacle
UPC	781786741904

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Installation Manual \[French, English\]](#)