



Straight Blade Devices, Receptacles, Duplex, Decorator Hospital Grade, Isolated Ground, 20A 125V, 2-Pole 3-Wire Grounding, Back and Side Wired, 5-20R

By Bryant
Catalog # 9300IGRED

Straight Blade Devices, Receptacles, Duplex, Decorator Hospital Grade, Isolated Ground, 20A 125V, 2-Pole 3-Wire Grounding, Back and Side Wired, 5-20R, Red, Single Pack

Features

- Duplex
- Decorator Hospital Grade
- Isolated Ground
- 20A 125V
- 2-Pole 3-Wire Grounding

Application

Hospital Grade

Specifications


Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	5-20R

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

Current

Current Rating	20 A
Amperage Rating	20 A
Voltage Rating Description	125 V
Phase	Single Phase
Current / Amperage Rating	20 A



Connectivity	Back and Side Wired
Wattage	2500
Voltage Rating	125 V

Dimensions

Display Size	Standard Sized Product
Weight	0.2 lb.

General

Series	Straight Blade
OEM Brand Name	Hubbell Bryant
Style	Decorator
Color	Red
Item Type	Decorator Duplex
Material - Mounting Hardware	Screw Mounting
Type	Single Receptacle
Material	Composite
UPC	781786741843

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Installation Manual \[French, English\]](#)