



Straight Blade Devices, Receptacles, Flush Mount Single, Commercial/Industrial Grade, Thermoset, Side Wired, 20A 250V

By Bryant
Catalog # 9326

Straight Blade Devices, Receptacles, Flush Mount Single, Commercial/Industrial Grade, Thermoset, Side Wired, 20A 250V, 3-Pole 3-Wire Non- Grounding, 10-20R, Black, Single Pack

Features

- Flush Mount Single
- Commercial/Industrial Grade
- Thermoset
- Side Wired
- 20A 250V

Application

Industrial Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Standards - RoHS Compliance	CM
Status	
Nema Rating	10-20R

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG
Number Of Poles	3-Pole

Current

Current Rating	20 A
Amperage Rating	20 A



Voltage Rating Description	250 V
Phase	Single Phase
Current / Amperage Rating	20 A
Connectivity	Side Wired Only
Wattage	5000
Voltage Rating	250 V

Dimensions

Display Size	Standard Sized Product
Weight	0.1 lb.

General

Series	Heavy Duty
OEM Brand Name	Hubbell Bryant
Style	Finder Groove Face
Color	Black
Item Type	Single
Material - Mounting Hardware	Screw Mounting
Type	Single Receptacle
UPC	781786632462

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)