



Straight Blade Devices, Receptacles, Flush Mount Single, Commercial/Industrial Grade, Reinforced Thermoplastic Polyester, 50A 125V

By Bryant
Catalog # 9530IG



Straight Blade Devices, Receptacles, Flush Mount Single, Commercial/Industrial Grade, Reinforced Thermoplastic Polyester, 50A 125V, 2-Pole 3-Wire Grounding, 5-50R, Orange, Single Pack, Isolated Ground

Features

- Flush Mount Single
- Commercial/Industrial Grade
- Reinforced Thermoplastic Polyester
- 50A 125V
- 2-Pole 3-Wire Grounding

Application

Industrial Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Industry Standard(s)	WR Rating
Nema Rating	5-30R

Conductor

Number Of Wires	3-Wire
Wire Size	#10 AWG to #6 AWG
Number Of Poles	2-Pole

Current

Current Rating	30 A
Amperage Rating	30 A
Voltage Rating Description	125 V
Phase	Single Phase

Current / Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Wattage	3750
Voltage Rating	125 V

Dimensions

Display Size	Standard Sized Product
Weight	0.4 lb.

General

Series	Straight Blade
OEM Brand Name	Hubbell Bryant
Style	Extra Heavy Duty
Color	Orange
Item Type	Single
Material - Mounting Hardware	Screw Mounting
Type	Single Receptacle
Material	Composite
UPC	781786731066

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)