



Straight Blade Devices, Female Connector Body, Heavy Duty, Industrial/Commercial Grade, Straight, 30A 125V, 2-Pole 3- Wire Grounding, 5-30R

By Bryant
Catalog # [9530NC](#)

Straight Blade Devices, Female Connector Body, Heavy Duty, Industrial/Commercial Grade, Straight, 30A 125V, 2-Pole 3- Wire Grounding, 5-30R, Gray, Single Pack

Features

- Heavy Duty
- Industrial/Commercial Grade
- Straight
- 30A 125V
- 2-Pole 3- Wire Grounding

Application

Heavy Duty

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Nema Rating	5-30R

Conductor

Number Of Wires	3-Wire
Number Of Conductors	3-Wire Grounding
Conductor Range	#12 AWG to #8 AWG
Number Of Poles	2-Pole

Current

Current Rating	30 A
Amperage Rating	30 A
Voltage Rating Description	125 V
Current / Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Voltage Rating	125 V



Dimensions

Display Size	Standard Sized Product
Weight	1.15 lb.

General

Series	Industrial
OEM Brand Name	Hubbell Bryant
Style	Extra Heavy Duty
Color	Gray
Item Type	Standard
Insulation	Insulated Body
Material - Mounting Hardware	Cord Mounted
Type	Connector Body
Material	Composite
UPC	781786731974

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	<ul style="list-style-type: none">• Maximum Continuous: 75° C• Minimum Continuous: -40° C w/o impact, -25° with impact.
--------------------	--

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)