



Straight Blade Devices, Receptacles, Flush Mount Single, Commercial/Industrial Grade, Reinforced Thermoplastic Polyester, 50A 125V, 5-50R

By Bryant
Catalog # 9550FR

Straight Blade Devices, Receptacles, Flush Mount Single, Commercial/Industrial Grade, Reinforced Thermoplastic Polyester, 50A 125V, 2-Pole 3-Wire Grounding, 5-50R, Black, Single Pack

Features

- Flush Mount Single
- Commercial/Industrial Grade
- Reinforced Thermoplastic Polyester
- 50A 125V
- 2-Pole 3-Wire Grounding

Application

Industrial Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Nema Rating	5-50R
Buy America(n) Qualified	BABA Compliant (All status valid till December 2026)
Industry Standard(s)	WR Rating

Conductor

Number Of Wires	3-Wire
Wire Size	#10 AWG to #6 AWG
Number Of Poles	2-Pole

Current

Amperage Rating	50 A
Voltage Rating Description	125 V
Current Rating	50 A



Voltage Rating	125 V
Wattage	6250
Connectivity	Pressure Terminal Screws
Phase	Single Phase
Current / Amperage Rating	50 A

Dimensions

Display Size	Standard Sized Product
Weight	0.45 lb.

General

Color	Black
Style	Smooth Face
Series	Heavy Duty
OEM Brand Name	Hubbell Bryant
UPC	781786676886
Type	Single Receptacle
Material - Mounting Hardware	Screw Mounting
Item Type	Single

Logistics

Carton Quantity	25
-----------------	----

Product Assets

- [Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Catalog Page \[English\]](#)