



Straight Blade Devices, Receptacles, Flush Mount Single, Commercial/Industrial Grade, Reinforced Thermoplastic Polyester, 30A 250V, 6-30R

By Bryant
Catalog # 9630FR



Straight Blade Devices, Receptacles, Flush Mount Single, Commercial/Industrial Grade, Reinforced Thermoplastic Polyester, 30A 250V, 2-Pole 3-Wire Grounding, 6-30R, Black, Single Pack

Features

- Flush Mount Single
- Commercial/Industrial Grade
- Reinforced Thermoplastic Polyester
- 30A 250V
- 2-Pole 3-Wire Grounding

Application

Industrial Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Standards - RoHS Compliance Status	CM
Industry Standard(s)	WR Rating
Nema Rating	6-30R
Buy America(n) Qualified	BABA Compliant (All status valid till December 2025)

Conductor

Number Of Wires	3-Wire
Wire Size	#10 AWG to #6 AWG
Number Of Poles	2-Pole

Current

Current Rating	30 A
----------------	------

Amperage Rating	30 A
Voltage Rating Description	250 V
Phase	Single Phase
Current / Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Wattage	7500
Voltage Rating	250 V

Dimensions

Display Size	Standard Sized Product
Weight	0.45 lb.

General

Series	Heavy Duty
OEM Brand Name	Hubbell Bryant
Style	Smooth Face
Color	Black
Item Type	Single
Material - Mounting Hardware Type	Screw Mounting Single Receptacle
UPC	781786677289

Logistics

Carton Quantity	25
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)