



## Straight Blade Devices, Female Connector Body, Heavy Duty, Industrial/Commercial Grade, Straight, 30A 250V, 2-Pole 3- Wire Grounding, 6-30R

By Bryant  
Catalog # [9630NC](#)

Straight Blade Devices, Female Connector Body, Heavy Duty, Industrial/Commercial Grade, Straight, 30A 250V, 2-Pole 3- Wire Grounding, 6-30R, Gray, Single Pack

### Features

- Heavy Duty
- Industrial/Commercial Grade
- Straight
- 30A 250V
- 2-Pole 3- Wire Grounding

### Application

Heavy Duty

### Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	6-30R

### Conductor

Number Of Wires	3-Wire
Number Of Conductors	3-Wire Grounding
Conductor Range	#12 AWG to #8 AWG
Number Of Poles	2-Pole

### Current

Current Rating	30 A
Amperage Rating	30 A
Voltage Rating Description	250 V
Current / Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Voltage Rating	250 V



### Dimensions

Display Size	Standard Sized Product
Length	5.19 in
Width	2.59 in
Weight	1.15 lb.

### General

Series	Industrial
OEM Brand Name	Hubbell Bryant
Style	Extra Heavy Duty
Color	Gray
Item Type	Standard
Insulation	Insulated Body
Material - Mounting Hardware	Cord Mounted
Type	Connector Body
Material	Composite
UPC	781786732223

### Logistics

Carton Quantity	10
-----------------	----

### Operational

Temperature Rating	<ul style="list-style-type: none"><li>• Maximum Continuous: 75° C</li><li>• Minimum Continuous: -40° C w/o impact, -25° with impact.</li></ul>
--------------------	--

### Product Assets

[Catalog \[English\]](#)  
[Catalog Page \[English\]](#)