



Straight Blade Devices, Female Connector Body, Heavy Duty, Industrial/Commercial Grade, Straight, 15A 125V, 2-Pole 2- Wire Non-Grounding, 1-15R

By Bryant
Catalog # [9755N](#)

Straight Blade Devices, Female Connector Body, Heavy Duty, Industrial/Commercial Grade, Straight, 15A 125V, 2-Pole 2- Wire Non-Grounding, 1-15R, White, Single Pack



Features

- Heavy Duty
- Industrial/Commercial Grade
- Straight
- 15A 125V
- 2-Pole 2- Wire Non-Grounding

Application

Heavy Duty

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	1-15R

Conductor

Number Of Wires	2-Wire
Number Of Conductors	2-Wire Non-Grounding
Conductor Range	#14 AWG to #10 AWG
Number Of Poles	2-Pole

Current

Current Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	125 V
Current / Amperage Rating	15 A
Connectivity	Pressure Terminal Screws
Voltage Rating	125 V

Dimensions

Display Size	Standard Sized Product
Length	2.62 in
Width	1.12 in
Weight	0.05 lb.

General

Series	Industrial
OEM Brand Name	Hubbell Bryant
Style	Heavy Duty
Color	Black and White
Item Type	Standard
Insulation	Insulated Body
Material - Mounting Hardware	Cord Mounted Plug
Type	Plug
Material	Composite
UPC	781786730359

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	<ul style="list-style-type: none">• Maximum Continuous: 75° C• Minimum Continuous: -40° C w/o impact, -25° with impact.
--------------------	--

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)