



Locking Devices, Locking Devices,
Industrial, Male Plug, 20A 250V, 2-Pole 3-
Wire Grounding, Non-NEMA, Screw
Terminal, Black

By Bryant
Catalog # 9965

Locking Devices, Locking Devices, Industrial, Male Plug, 20A
250V, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal,
Black

Features

- Male Nylon Plug
- 20A 125/250V AC
- 3-Pole 3-Wire Non-Grounding
- Non-NEMA
- Screw Terminal

Application

Extra Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	Non-NEMA

Conductor

Number Of Wires	3-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Poles	3-Pole

Configuration

Cord Type	All Listed Portables
-----------	----------------------

Current

Current/Amperage Rating	20 Amp
Description	
Current Rating	20 A
Amperage Rating	20 A



Voltage Rating Description	125/250 VAC
Phase	Single Phase
Connectivity	Screw Terminals
Voltage Rating	125/250 VAC

Dimensions

Display Size	Standard Sized
Length	2.11 in
Width	2.11 in
Height	2.60 in
Dimensions	2.11 in x 2.11 in x 2.60 in

General

OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Color	Black, White
Item Type	20A Nylon Plug-For Replacement Use
Material - Mounting Hardware	Cord Mounted
Type	Plugs
Material	Composite
UPC	781786633759

Logistics

Carton Quantity	10
Pallet Quantity	2340

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)