



Locking Devices, Locking Devices,
Industrial, Male Plug, 20A 125/250V, 3-Pole
3-Wire Non Grounding, Non-NEMA, Screw
Terminal, Black

By Bryant
Catalog # 9965NB

Locking Devices, Locking Devices, Industrial, Male Plug, 20A
125/250V, 3-Pole 3-Wire Non Grounding, Non-NEMA, Screw
Terminal, Black

Features

- Male Nylon Plug
- 20A 125/250V AC
- 3-Pole 3-Wire Non-Grounding
- Non-NEMA
- Screw Terminal

Application

Extra Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Nema Rating	Non-NEMA

Conductor

Number Of Wires	3-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Poles	3-Pole

Configuration

Cord Type	All Listed Portables
-----------	----------------------

Current

Current/Amperage Rating	20 Amp
Description	
Current Rating	20 A
Amperage Rating	20 A



Voltage Rating Description	125/250 VAC
Phase	Single Phase
Connectivity	Screw Terminals
Voltage Rating	125/250 VAC

Dimensions

Display Size	Standard Sized
Length	2.11 in
Width	2.11 in
Height	2.60 in
Dimensions	2.11 in x 2.11 in x 2.60 in

General

OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Color	All Black
Item Type	Nylon Plug-For Replacement Use
Material - Mounting Hardware	Cord Mounted
Type	Plugs
Material	Composite
UPC	781786616868

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)