

Straight Blade Devices, Elastomeric, Male Plug, 20A 125V, 2-Pole 3-Wire Grounding, 5-20P, Screw Terminal, Yellow, Water/Dust-Tight Housing

By Bryant

Catalog # [BRY14W33](#)

Straight Blade Devices, Elastomeric, Male Plug, 20A 125V, 2-Pole 3-Wire Grounding, 5-20P, Screw Terminal, Yellow, Water/Dust-Tight Housing



Features

- Male
- 20A 125V
- 2-Pole 3-Wire Grounding
- 5-20P
- Screw Terminal

Specifications

Nema Rating	5-20P
Standards - RoHS Compliance Status	CM

Conductor

Number Of Wires	3-Wire
Number Of Poles	2-Pole

Current

Current / Amperage Rating	20 A
Amperage Rating	20 A
Voltage Rating Description	125 V

Voltage Rating	125 V
----------------	-------

Dimensions

Width	1.85 in
Weight	0.5 lb.
Length	3.16 in

General

Type	Plug
OEM Brand Name	Hubbell Bryant
Cord Range	0.325"-0.625"
UPC	781786378155
Color	Yellow

Logistics

Carton Quantity	25
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)