



Straight Blade Devices, Elastomeric, Female Connector Body, 20A 125V, 2-Pole 3-Wire Grounding, 5-20P, Screw Terminal, Yellow, Water/Dust-Tight Housing

By Bryant

Catalog # [BRY15W33](#)

Straight Blade Devices, Elastomeric, Female Connector Body, 20A 125V, 2-Pole 3-Wire Grounding, 5-20P, Screw Terminal, Yellow, Water/Dust-Tight Housing

Features

- Female Connector Body
- 20A 125V
- 2-Pole 3-Wire Grounding
- 5-20P
- Screw Terminal

Specifications

Nema Rating	5-20R
Standards - RoHS Compliance Status	CM

Conductor

Number Of Wires	3-Wire
Number Of Poles	2-Pole

Current

Current / Amperage Rating	20 A
Amperage Rating	20 A



Voltage Rating Description	125 V
Voltage Rating	125 V

Dimensions

Width	1.85 in
Weight	0.3 lb.
Length	4.42 in

General

Type	Connector Body
Cord Range	0.325"-0.625"
UPC	781786378223
Color	Yellow

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Catalog \[English\]](#)