



Straight Blade Devices, Elastomeric,
Female Connector Body, 15A 125V, 2-Pole
3-Wire Grounding, 5-15P, Screw Terminal,
Black, Water/Dust-Tight Housing

By Bryant
Catalog # [BRY15W47BK](#)

Straight Blade Devices, Elastomeric, Female Connector Body, 15A
125V, 2-Pole 3-Wire Grounding, 5-15P, Screw Terminal, Black,
Water/Dust-Tight Housing

Features

- Female Connector Body
- 15A 125V
- 2-Pole 3-Wire Grounding
- 5-15P
- Screw Terminal

Specifications

Nema Rating5-15R

Conductor

Number Of Wires3-Wire
Number Of Poles2-Pole

Current

Current / Amperage Rating15 A
Amperage Rating15 A
Voltage Rating Description125 V
Voltage Rating125 V



Dimensions

Width1.85 in
Weight0.3 lb.
Length4.42 in

General

TypeConnector Body
OEM Brand NameHubbell Bryant
Cord Range0.325"-0.625"
UPC781786378193
StyleStraight
ColorBlack

Logistics

Carton Quantity10

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)