



Straight Blade Devices, Elastomeric,
Female Connector Body Interior, 15A 125V,
5-15R, Screw Terminal, Water/Dust-Tight
Housing

By Bryant
Catalog # [BRY15W47IN](#)

Straight Blade Devices, Elastomeric, Female Connector Body
Interior, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Screw
Terminal, Black, Water/Dust-Tight Housing

Features

- Female Connector Body Interior
- 15A 125V
- 2-Pole 3-Wire Grounding
- 5-15R
- Screw Terminal

Specifications

Nema Rating 5-15R

Conductor

Number Of Wires 3-Wire
Number Of Poles 2-Pole

Current

Current / Amperage Rating 15 A



Amperage Rating 15 A
Voltage Rating Description 125 V
Voltage Rating 125 V

General

Type Interiors
OEM Brand Name Hubbell Bryant
UPC 781786378209
Color White

Logistics

Carton Quantity 10

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)