



Straight Blade Devices, Elastomeric,
Female Connector Body, 15A 250V, 2-Pole
3-Wire Grounding, 6-15P, Screw Terminal,
Yellow, Water/Dust-Tight Housing

By Bryant
Catalog # [BRY15W49](#)

Straight Blade Devices, Elastomeric, Female Connector Body, 15A
250V, 2-Pole 3-Wire Grounding, 6-15P, Screw Terminal, Yellow,
Water/Dust-Tight Housing

Features

- Female Connector Body
- 15A 250V
- 2-Pole 3-Wire Grounding
- 6-15P
- Screw Terminal

Specifications

Nema Rating6-15R

Conductor

Number Of Wires3-Wire
Number Of Poles2-Pole

Current

Current / Amperage Rating15 A
Amperage Rating15 A
Voltage Rating Description250 V
Voltage Rating250 V



Dimensions

Width1.85 in
Weight0.3 lb.
Length4.42 in

General

TypeConnector Body
OEM Brand NameHubbell Bryant
Cord Range0.325"-0.625"
UPC781786378216
StyleStraight
ColorYellow

Logistics

Carton Quantity10

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)