



Temporary Lighting Products, 100' 18/2
STW, Straight Blade, With 10) 6.6W 90 LED
Fixture, 450 Lumen Output Per Fixture

By Bryant
Catalog # [BRY182S100LED](#)

Temporary Lighting Products, 100' 18/2 STW, Straight Blade,
With 10) 6.6W 90 LED Fixture, 450 Lumen Output Per Fixture

Features

- Straight Blade
- With 10) 6.6W 90 LED Fixture
- 450 Lumen Output Per Fixture

Current

Current / Amperage Rating	15 A
Voltage Rating	125 VAC



General

Type	LED
Series	Stringer Lights
UPC	781786380097
Light Source	LED

Product Assets

- [Catalog \[English\]](#)
[Catalog Page \[English\]](#)