



Temporary Lighting Products, 50' 18/2
STW Light String, With 5) 6.6W 90 LED,
450 Lumen Output Per Fixture

By Bryant
Catalog # [BRY182S50LED](#)

Temporary Lighting Products, 50' 18/2 STW Light String, With 5)
6.6W 90 LED, 450 Lumen Output Per Fixture

Features

- With 5) 6.6W 90 LED
- 450 Lumen Output Per Fixture

Current

Current / Amperage Rating	15 A
Voltage Rating	125 VAC

General



Type	LED
Series	Stringer Lights
UPC	781786380080
Light Source	LED

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)