



# Locking Devices, Male Plug, 15A 277V AC, 2-Pole 3-Wire Grounding, L7-15P, Screw Terminal, Yellow, Water/Dust-Tight Housing

By Bryant  
Catalog # [BRY24W34](#)



Locking Devices, Male Plug, 15A 277V AC, 2-Pole 3-Wire Grounding, L7-15P, Screw Terminal, Yellow, Water/Dust-Tight Housing

## Features

- Triple bypass seal keeps water away from electrical connections and works with previously installed devices
- Corrosion-resistant connection points
- High conductivity brass termination
- Cone seal accomodates any cable range
- Keyed interior for easy installation

## Performance

Dielectric voltage:2000V AC if rated 300V or less, 3000V AC if rated above 300V, Moisture resistance:UL Listed to 3R, 3RX, 4, 4X, 6, 6P, 12, UV resistance:All exposed materials are UV stabilized, Flammability:UL94V2 (plugs, connectors, and interiors)

## Specifications

Industry Standard(s)	<ul style="list-style-type: none"> <li>• IP69K</li> <li>• Listed to UL498</li> <li>• Certified to CSA C22.2 No. 42</li> <li>• Meets NEMA® WD-1, WD-6, and ANSI Standards</li> <li>• IP66 Suitability</li> <li>• NSF Certified (plugs, connectors and receptacles)</li> </ul>
Nema Rating	L7-15P
<b>Conductor</b>	
Number Of Wires	3-Wire

Wire Size	#16/3 SJ to #10/3 SJ, #18/3 S to #12/3 S
Number Of Poles	2-Pole

## Current

Current/Amperage Rating	15 Amp
Description	
Amperage Rating	15 A
Voltage Rating Description	277 VAC
Voltage Rating	277 VAC

## Dimensions

Width	1.85 in
Height	3.21 in
Length	1.85 in
Dimensions	1.85 in x 1.85 in x 3.21 in

## General

Item Type	15A Watertight Plug
Type	Plugs
UPC	781786378261
Color	Yellow

## Logistics

Carton Quantity	25
-----------------	----

## Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)