

## Locking Devices, Elastomeric, Female Connector Body, 15A277V AC, 2-Pole 3-Wire Grounding, L7-15R, Screw Terminal, Yellow, Water/Dust-Tight Housing



By Bryant  
Catalog # [BRY25W34](#)

Locking Devices, Elastomeric, Female Connector Body, 15A277V AC, 2-Pole 3-Wire Grounding, L7-15R, Screw Terminal, Yellow, Water/Dust-Tight Housing

### Features

- Smooth body design minimizes collection points simplifying the wash down process
- Free-floating cap allows unwanted material to wash away during sanitation
- Unique cone seal prevents dirt and debris from collecting at the cable entrance
- PBT strain relief nut provides unparalleled impact resistance

### Performance

Dielectric voltage:2000V AC if rated 300V or less, 3000V AC if rated above 300V, Moisture resistance:UL Listed to 3R, 3RX, 4, 4X, 6, 6P, 12, UV resistance:All exposed materials are UV stabilized, Flammability:UL94V2 (plugs, connectors, and interiors)

### Specifications

Industry Standard(s)	<ul style="list-style-type: none"> <li>• IP69K</li> <li>• Listed to UL498</li> <li>• Certified to CSA C22.2 No. 42</li> <li>• Meets NEMA® WD-1, WD-6, and ANSI Standards</li> <li>• IP66 Suitability</li> <li>• NSF Certified (plugs, connectors and receptacles)</li> </ul>
Nema Rating	L7-15R

### Conductor

Number Of Wires	3-Wire
Wire Size	#16/3 SJ to #10/3 SJ, #18/3 S to #12/3 S
Number Of Poles	2-Pole

### Current

Current/Amperage Rating	15 Amp
Description	
Amperage Rating	15 A
Voltage Rating Description	277 VAC
Voltage Rating	277 VAC

### Dimensions

Width	1.85 in
Height	4.62 in
Length	1.85 in
Dimensions	1.85 in x 1.85 in x 4.62 in

### General

Item Type	15A Watertight Connector
Type	Connector Body
UPC	781786378315
Color	Yellow

### Logistics

Carton Quantity	25
-----------------	----

### Product Assets

[Catalog \[English\]](#)