



Locking Devices, Elastomeric, Female Connector Body, 15A 125V, 2-Pole 3-Wire Grounding, L5-15R, Screw Terminal, Black, Water/Dust-Tight Housing

By Bryant
Catalog # [BRY25W47BK](#)

Watertight Devices, Locking Devices, Elastomeric, Female Connector Body, 15A 125V, 2-Pole 3-Wire Grounding, L5-15R, Screw Terminal, Black, Water/Dust-Tight Housing

Features

- Smooth body design minimizes collection points simplifying the wash down process
- Free-floating cap allows unwanted material to wash away during sanitation
- Unique cone seal prevents dirt and debris from collecting at the cable entrance
- PBT strain relief nut provides unparalleled impact resistance

Performance

Dielectric voltage:2000V AC if rated 300V or less, 3000V AC if rated above 300V, Moisture resistance:UL Listed to 3R, 3RX, 4, 4X, 6, 6P, 12, UV resistance:All exposed materials are UV stabilized, Flammability:UL94V2 (plugs, connectors, and interiors)

Specifications

Nema Rating L5-15R

Conductor

Number Of Poles 2-Pole
Number Of Wires 3-Wire



Wire Size #16/3 SJ to #10/3 SJ, #18/3 S to #12/3 S

Current

Current/Amperage Rating 15 Amp
Description
Amperage Rating 15 A
Voltage Rating Description 125 V
Voltage Rating 125 V

Dimensions

Width 1.85 in
Height 4.62 in
Length 1.85 in
Dimensions 1.85 in x 1.85 in x 4.62 in

General

Item Type 15A Watertight Connector
Type Connector Body
Color Black

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)