



Locking Devices, Elastomeric, Female Connector Body, 15A 250V, 2-Pole 3-Wire Grounding, L6-15R, Screw Terminal, Yellow, Water/Dust-Tight Housing

By Bryant
Catalog # BRY25W49

Locking Devices, Elastomeric, Female Connector Body, 15A 250V, 2-Pole 3-Wire Grounding, L6-15R, Screw Terminal, Yellow,Water/Dust-Tight Housing

Features

- Smooth body design minimizes collection points simplifying the wash down process
- Free-floating cap allows unwanted material to wash away during sanitation
- Unique cone seal prevents dirt and debris from collecting at the cable entrance
- PBT strain relief nut provides unparalleled impact resistance

Performance

Dielectric voltage:2000V AC if rated 300V or less, 3000V AC if rated above 300V, Moisture resistance:UL Listed to 3R, 3RX, 4, 4X, 6, 6P, 12, UV resistance:All exposed materials are UV stabilized, Flammability:UL94V2 (plugs, connectors, and interiors)

Specifications

Industry Standard(s)	• IP69K • Listed to UL498 • Certified to CSA C22.2 No. 42 • Meets NEMA® WD-1, WD-6, and ANSI Standards • IP66 Suitability • NSF Certified (plugs, connectors and receptacles)
Nema Rating	L6-15R
Conductor	
Number Of Wires	3-Wire



Wire Size	#16/3 SJ to #10/3 SJ, #18/3 S to #12/3 S
Number Of Poles	2-Pole

Current

Current/Amperage Rating Description	15 Amp
Amperage Rating	15 A
Voltage Rating Description	250 V
Voltage Rating	250 V

Dimensions

Width	1.85 in
Height	4.62 in
Length	1.85 in
Dimensions	1.85 in x 1.85 in x 4.62 in

General

Item Type	15A Watertight Connector
Type	Connector Body
UPC	781786378339
Color	Yellow

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)