



Straight Blade Devices, Female Connector Body, Elastomeric Water Tight, Industrial/Commercial Grade, Straight, 20A 125/250V, Non-NEMA

By Bryant
Catalog # [BRY26W08](#)

Straight Blade Devices, Female Connector Body, Elastomeric Water Tight, Industrial/Commercial Grade, Straight, 2-Pole 3-Wire Grounding, 20A 125/250V, Non-NEMA, Single Pack

Features

- Triple bypass seal keeps water away from electrical connections and works with previously installed devices
- Corrosion-resistant connection points
- High conductivity brass termination
- Cone seal accomodates any cable range
- Keyed interior for easy installation

Specifications

Industry Standard(s)	IP69K
Nema Rating	Non-NEMA
Conductor	
Number Of Wires	3-Wire
Wire Size	• Min. cord: #16/3 SJ, #18/3 S, #18/4 SJ, #18/4 S, #18/5 S • Max. cord: #10/3 S, #10/4 S, #10/5 S
Number Of Poles	3-Pole

Current

Current/Amperage Rating	20 Amp
Description	



Amperage Rating	20 A
Voltage Rating Description	125/250 VAC
Voltage Rating	125/250 VAC

Dimensions

Width	2.51 in
Height	3.96 in
Length	2.51 in
Dimensions	2.51 in x 2.51 in x 3.96 in

General

Item Type	20A Watertight Plug
Type	Plugs
UPC	781786378360
Color	Yellow

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)