

## Locking Devices, Elastomeric, Male Plug, 20A 250V, 2-Pole 3-Wire Grounding, L6-20P, Screw Terminal, Yellow, Water/Dust-Tight Housing

By Bryant  
 Catalog # [BRY26W48](#)



Locking Devices, Elastomeric, Male Plug, 20A 250V, 2-Pole 3-Wire Grounding, L6-20P, Screw Terminal, Yellow, Water/Dust-Tight Housing

### Features

- Triple bypass seal keeps water away from electrical connections and works with previously installed devices
- Corrosion-resistant connection points
- High conductivity brass termination
- Cone seal accomodates any cable range
- Keyed interior for easy installation

### Performance

Dielectric voltage:2000V AC if rated 300V or less, 3000V AC if rated above 300V, Moisture resistance:UL Listed to 3R, 3RX, 4, 4X, 6, 6P, 12, UV resistance:All exposed materials are UV stabilized, Flammability:UL94V2 (plugs, connectors, and interiors)

### Specifications

Standards - RoHS Compliance Status	CM
Industry Standard(s)	<ul style="list-style-type: none"> <li>• IP69K</li> <li>• Listed to UL498</li> <li>• Certified to CSA C22.2 No. 42</li> <li>• Meets NEMA® WD-1, WD-6, and ANSI Standards</li> <li>• IP66 Suitability</li> <li>• NSF Certified (plugs, connectors and receptacles)</li> </ul>
Nema Rating	L6-20P
<b>Conductor</b>	
Number Of Wires	3-Wire

Wire Size	<ul style="list-style-type: none"> <li>• Min. cord: #16/3 SJ, #18/3 S, #18/4 SJ, #18/4 S, #18/5 S</li> <li>• Max. cord: #10/3 S, #10/4 S, #10/5 S</li> </ul>
Number Of Poles	2-Pole

### Current

Current/Amperage Rating	20 Amp
Description	
Amperage Rating	20 A
Voltage Rating Description	250 V
Voltage Rating	250 V

### Dimensions

Length	2.51 in
Width	2.51 in
Height	3.96 in
Dimensions	2.51 in x 2.51 in x 3.96 in

### General

Color	Yellow
Item Type	20A Watertight Plug
Type	Plugs
UPC	781786378384

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)