



Locking Devices, Elastomeric, Male Plug, 20A 125/250V, 3-Pole 3-Wire Non-Grounding, Non-NEMA, Screw Terminal, Yellow, Water/Dust-Tight Housing

By Bryant
Catalog # [BRY27W08](#)

Locking Devices, Elastomeric, Male Plug, 20A 125/250V, 3-Pole 3-Wire Non-Grounding, Non-NEMA, Screw Terminal, Yellow, Water/Dust-Tight Housing

Features

- Smooth body design minimizes collection points simplifying the wash down process
- Free-floating cap allows unwanted material to wash away during sanitation
- Unique cone seal prevents dirt and debris from collecting at the cable entrance
- PBT strain relief nut provides unparalleled impact resistance

Performance

Dielectric voltage:2000V AC if rated 300V or less, 3000V AC if rated above 300V, Moisture resistance:UL Listed to 3R, 3RX, 4, 4X, 6, 6P, 12, UV resistance:All exposed materials are UV stabilized, Flammability:UL94V2 (plugs, connectors, and interiors)

Specifications

Industry Standard(s)	• IP69K • Listed to UL498 • Certified to CSA C22.2 No. 42 • Meets NEMA® WD-1, WD-6, and ANSI Standards • IP66 Suitability • NSF Certified (plugs, connectors and receptacles)
Nema Rating	Non-NEMA

Conductor

Number Of Wires	3-Wire
-----------------	--------



Wire Size	• Min. cord: #16/3 SJ, #18/3 S, #18/4 SJ, #18/4 S, #18/5 S • Max. cord: #10/3 S, #10/4 S, #10/5 S
Number Of Poles	3-Pole

Current

Current/Amperage Rating Description	20 Amp
Amperage Rating	20 A
Voltage Rating Description	125/250 VAC
Voltage Rating	125/250 VAC

Dimensions

Width	2.51 in
Height	5.69 in
Length	2.51 in
Dimensions	2.51 in x 2.51 in x 5.69 in

General

Item Type	20A Watertight Connector
Type	Connector Body
UPC	781786378544
Color	Yellow

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)