



Locking Devices, Elastomeric, Female
Connector Body Interior, 20A 125V, 2-Pole
3-Wire Grounding, L5-20R, Screw Terminal,
Black

By Bryant
Catalog # [BRY27W47IN](#)

Locking Devices, Elastomeric, Female Connector Body Interior,
20A 125V, 2-Pole 3-Wire Grounding, L5-20R, Screw Terminal,
Black

Features

- Elastomeric
- Receptacle Interior
- 20A 125V
- 2-Pole 3-Wire Grounding
- L5-20R

Specifications

Nema Rating L5-20R

Conductor

Number Of Wires 3-Wire
Number Of Poles 2-Pole

Current

Current/Amperage Rating 20 Amp
Description



Amperage Rating 20 A
Voltage Rating Description 125 V
Voltage Rating 125 V

General

Item Type 20A 125V Watertight
 Receptacle Replacement
 Interior
Type Interiors
UPC 781786378520

Logistics

Carton Quantity 10

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)