

**Locking Devices, Elastomeric, Male Plug, 20A 125/250V, 3-Pole 4-Wire Grounding, L14-20R, Screw Terminal, Yellow Water/Dust Tight Housing**



By Bryant  
Catalog # [BRY27W74](#)

Locking Devices, Elastomeric, Male Plug, 20A 125/250V, 3-Pole 4-Wire Grounding, L14-20R, Screw Terminal, Yellow Water/Dust Tight Housing

**Features**

- Smooth body design minimizes collection points simplifying the wash down process
- Free-floating cap allows unwanted material to wash away during sanitation
- Unique cone seal prevents dirt and debris from collecting at the cable entrance
- PBT strain relief nut provides unparalleled impact resistance

**Performance**

Dielectric voltage:2000V AC if rated 300V or less, 3000V AC if rated above 300V, Moisture resistance:UL Listed to 3R, 3RX, 4, 4X, 6, 6P, 12, UV resistance:All exposed materials are UV stabilized, Flammability:UL94V2 (plugs, connectors, and interiors)

**Specifications**

Industry Standard(s)	<ul style="list-style-type: none"> <li>• IP69K</li> <li>• Listed to UL498</li> <li>• Certified to CSA C22.2 No. 42</li> <li>• Meets NEMA® WD-1, WD-6, and ANSI Standards</li> <li>• IP66 Suitability</li> <li>• NSF Certified (plugs, connectors and receptacles)</li> </ul>
Nema Rating	L14-20R

**Conductor**

Number Of Wires	4-Wire
-----------------	--------

Wire Size	<ul style="list-style-type: none"> <li>• Min. cord: #16/3 SJ, #18/3 S, #18/4 SJ, #18/4 S, #18/5 S</li> <li>• Max. cord: #10/3 S, #10/4 S, #10/5 S</li> </ul>
Number Of Poles	3-Pole

**Current**

Current/Amperage Rating Description	20 Amp
Amperage Rating	20 A
Voltage Rating Description	125/250 VAC
Voltage Rating	125/250 VAC

**Dimensions**

Width	2.51 in
Height	5.69 in
Length	2.51 in
Dimensions	2.51 in x 2.51 in x 5.69 in

**General**

Item Type	20A Watertight Connector
Type	Connector Body
UPC	781786378582
Color	Yellow

**Logistics**

Carton Quantity	10
-----------------	----

**Product Assets**

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)