



Locking Devices, Elastomeric, Male Plug,
30A 3- Phase 480V AC, 3-Pole 4-Wire
Grounding, L16-30P, Screw Terminal, Black,
Water/Dust-Tight Housing

By Bryant
Catalog # [BRY28W76BK](#)

Locking Devices, Elastomeric, Male Plug, 30A 3- Phase 480V AC,
3-Pole 4-Wire Grounding, L16-30P, Screw Terminal, Black
,Water/Dust-Tight Housing

Features

- Triple bypass seal keeps water away from electrical connections and works with previously installed devices
- Corrosion-resistant connection points
- High conductivity brass termination
- Cone seal accomodates any cable range
- Keyed interior for easy installation

Performance

Dielectric voltage:2000V AC if rated 300V or less, 3000V AC if rated above 300V, Moisture resistance:UL Listed to 3R, 3RX, 4, 4X, 6, 6P, 12, UV resistance:All exposed materials are UV stabilized, Flammability:UL94V2 (plugs, connectors, and interiors)

Specifications

Industry Standard(s)	• IP69K • Listed to UL498 • Certified to CSA C22.2 No. 42 • Meets NEMA® WD-1, WD-6, and ANSI Standards • IP66 Suitability • NSF Certified (plugs, connectors and receptacles)
Nema Rating	L16-30P

Conductor

Number Of Wires	4-Wire
Wire Size	• Min. cords: #12/3 SJ, #16/3 S, #14/4 SJ, #18/4 S, #18/5 S



Number Of Poles	• Max. cord: #8/3 S, #8/4 S, #10/5 S 3-Pole
-----------------	---

Current

Current/Amperage Rating	30 Amp
Description	
Amperage Rating	30 A
Voltage Rating Description	3 Phase 480 VAC
Voltage Rating	3 Phase 480 VAC

Dimensions

Width	2.77 in
Height	3.94 in
Length	2.77 in
Dimensions	2.77 in x 2.77 in x 3.94 in

General

Item Type	30A Watertight Plug
Type	Plugs
UPC	781786378803
Color	Black

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)