



Locking Devices, Elastomeric, Female Connector Body, 30A 125/250V, 3-Pole 4-Wire Grounding, L14-30R, Screw Terminal, Yellow, Water/Dust-Tight Housing

By Bryant
Catalog # [BRY29W74](#)

Locking Devices, Elastomeric, Female Connector Body, 30A 125/250V, 3-Pole 4-Wire Grounding, L14-30R, Screw Terminal ,Yellow, Water/Dust-Tight Housing

Features

- Smooth body design minimizes collection points simplifying the wash down process
- Free-floating cap allows unwanted material to wash away during sanitation
- Unique cone seal prevents dirt and debris from collecting at the cable entrance
- PBT strain relief nut provides unparalleled impact resistance

Performance

Dielectric voltage:2000V AC if rated 300V or less, 3000V AC if rated above 300V, Moisture resistance:UL Listed to 3R, 3RX, 4, 4X, 6, 6P, 12, UV resistance:All exposed materials are UV stabilized, Flammability:UL94V2 (plugs, connectors, and interiors)

Specifications

Industry Standard(s)	• IP69K • Listed to UL498 • Certified to CSA C22.2 No. 42 • Meets NEMA® WD-1, WD-6, and ANSI Standards • IP66 Suitability • NSF Certified (plugs, connectors and receptacles)
Nema Rating	L14-30R

Conductor

Number Of Wires	4-Wire
-----------------	--------



Wire Size	• Min. cords: #12/3 SJ, #16/3 S, #14/4 SJ, #18/4 S, #18/5 S • Max. cord: #8/3 S, #8/4 S, #10/5 S
Number Of Poles	3-Pole

Current

Current/Amperage Rating Description	30 Amp
Amperage Rating	30 A
Voltage Rating Description	125/250 VAC
Voltage Rating	125/250 VAC

Dimensions

Width	2.77 in
Height	5.67 in
Length	2.77 in
Dimensions	2.77 in x 2.77 in x 5.67 in

General

Item Type	30A Watertight Connector
Type	Connector Body
UPC	781786378681
Color	Yellow

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)