



Locking Devices, Elastomeric, Female
Connector Body Interior, 30A 3-Phase
Delta 250V AC, 3-Pole 4-Wire Grounding,
L15- 30R, Screw Terminal

By Bryant
Catalog # [BRY29W75IN](#)

Locking Devices, Elastomeric, Female Connector Body Interior,
30A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, L15- 30R,
Screw Terminal

Features

- Elastomeric
- Receptacle Interior
- 30A 3-Phase Delta 250V AC
- 3-Pole 4-Wire Grounding
- L15- 30R

Specifications

Nema Rating L15-30R

Conductor

Number Of Wires 4-Wire
Number Of Poles 3-Pole

Current

Current/Amperage Rating 30 Amp
Description



Amperage Rating 30 A
Voltage Rating Description 3 Phase 250 VAC
Voltage Rating 3 Phase 250 VAC

General

Item Type 30A 250V Watertight
 Receptacle Replacement
 Interior
Type Interiors
UPC 781786378940

Logistics

Carton Quantity 10

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)