



Locking Devices, Elastomeric, Female Connector Body, 30A 3-Phase Delta 600V AC, 3-Pole 4-Wire Grounding, L17-30R, Water/Dust-Tight Housing

By Bryant  
Catalog # [BRY29W77](#)

Locking Devices, Elastomeric, Female Connector Body, 30A 3-Phase Delta 600V AC, 3-Pole 4-Wire Grounding, L17-30R, Screw Terminal, Yellow, Water/Dust-Tight Housing

Features

- Smooth body design minimizes collection points simplifying the wash down process
- Free-floating cap allows unwanted material to wash away during sanitation
- Unique cone seal prevents dirt and debris from collecting at the cable entrance
- PBT strain relief nut provides unparalleled impact resistance

Performance

Dielectric voltage:2000V AC if rated 300V or less, 3000V AC if rated above 300V, Moisture resistance:UL Listed to 3R, 3RX, 4, 4X, 6, 6P, 12, UV resistance:All exposed materials are UV stabilized, Flammability:UL94V2 (plugs, connectors, and interiors)

Specifications

|                      |                                                                                                                                                                                                                                                                       |
|----------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Industry Standard(s) | <ul style="list-style-type: none"><li>• IP69K</li><li>• Listed to UL498</li><li>• Certified to CSA C22.2 No. 42</li><li>• Meets NEMA® WD-1, WD-6, and ANSI Standards</li><li>• IP66 Suitability</li><li>• NSF Certified (plugs, connectors and receptacles)</li></ul> |
| Nema Rating          | L17-30R                                                                                                                                                                                                                                                               |

Conductor

|                 |        |
|-----------------|--------|
| Number Of Wires | 3-Wire |
|-----------------|--------|



|                 |                                                                                                                                                          |
|-----------------|----------------------------------------------------------------------------------------------------------------------------------------------------------|
| Wire Size       | <ul style="list-style-type: none"><li>• Min. cords: #12/3 SJ, #16/3 S, #14/4 SJ, #18/4 S, #18/5 S</li><li>• Max. cord: #8/3 S, #8/4 S, #10/5 S</li></ul> |
| Number Of Poles | 3-Pole                                                                                                                                                   |

Current

|                            |                 |
|----------------------------|-----------------|
| Current/Amperage Rating    | 30 Amp          |
| Description                |                 |
| Amperage Rating            | 30 A            |
| Voltage Rating Description | 3 Phase 600 VAC |
| Voltage Rating             | 3 Phase 600 VAC |

Dimensions

|            |                             |
|------------|-----------------------------|
| Width      | 2.77 in                     |
| Height     | 5.67 in                     |
| Length     | 2.77 in                     |
| Dimensions | 2.77 in x 2.77 in x 5.67 in |

General

|           |                          |
|-----------|--------------------------|
| Item Type | 30A Watertight Connector |
| Type      | Connector Body           |
| UPC       | 781786378995             |
| Color     | Yellow                   |

Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

[Catalog \[English\]](#)  
[Catalog Page \[English\]](#)