



Straight Blade Devices, Receptacles,
Duplex, Commercial/Industrial Grade, 15A
125V, 2-Pole 3-Wire Grounding, 5-15R, Ivory,
Single Pack

By Bryant
Catalog # [BRY5262I](#)

Straight Blade Devices, Receptacles, Duplex,
Commercial/Industrial Grade, 15A 125V, 2-Pole 3-Wire Grounding,
5-15R, Ivory, Single Pack

Features

- Duplex
- Commercial/Industrial Grade
- 15A 125V
- 2-Pole 3-Wire Grounding
- 5-15R

Application

Extra Heavy Duty Industrial Specification Grade

Specifications


Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	5-15R

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

Current

Current Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	125 V
Phase	Single Phase
Current / Amperage Rating	15 A
Connectivity	Back and Side Wired



Wattage	1875
Voltage Rating	125 V

Dimensions

Display Size	Standard Sized Product
Length	3.28 in
Width	1.54 in
Weight	0.2 lb.
Height	1.16 in
Dimensions	3.28 in x 1.54 in x 1.16 in

General

Series	Extra Heavy Duty
OEM Brand Name	Hubbell Bryant
Style	Finder Groove Face
Color	Ivory
Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Type	Duplex Receptacle
UPC	781786005044

Logistics

Carton Quantity	10
Pallet Quantity	5500

Product Assets

- [Catalog \[English\]](#)
[Catalog Page \[English\]](#)