



## Straight Blade Devices, Male Plug, Heavy Duty, Industrial/Commercial Grade, Straight, 15A 125V, 2-Pole 3-Wire Grounding, 5-15P and Black, Single Pack

By Bryant  
Catalog # [BRY5266NP](#)

Straight Blade Devices, Male Plug, Heavy Duty,  
Industrial/Commercial Grade, Straight, 15A 125V, 2-Pole 3-Wire  
Grounding, 5-15P, White and Black, Single Pack



### Features

- Heavy Duty
- Industrial/Commercial Grade
- Straight
- 15A 125V
- 2-Pole 3-Wire Grounding

### Application

Extra Heavy Duty Industrial Grade

### Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Standards - RoHS Compliance Status	CM
Nema Rating	5-15P

### Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

### Configuration

Cord Type	All Portable
-----------	--------------

### Current

Current Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	125 V
Phase	Single Phase

Current / Amperage Rating	15 A
Connectivity	Screw Terminals
Wattage	1875
Voltage Rating	125 V

### Dimensions

Display Size	Standard Sized
Length	2.18 in
Width	1.52 in
Weight	0.2 lb.
Height	1.38 in
Dimensions	2.18 in x 1.52 in x 1.38 in

### General

Series	Industrial
OEM Brand Name	Hubbell Bryant
Style	Extra Heavy Duty
Color	Black and White
Item Type	Tech-Spec Triple Gripper
Material - Mounting Hardware	Cord Mounted
Type	Plug
Material	Composite
UPC	781786005877

### Logistics

Carton Quantity	10
Pallet Quantity	4000

### Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)