



Straight Blade Devices, Receptacles, Combo Duplex, Commercial/Industrial Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5- 15R, Brown, Single Pack

By Bryant
Catalog # [BRY5292](#)



Straight Blade Devices, Receptacles, Combo Duplex,
Commercial/Industrial Grade, 15A 125V, 2-Pole 3-Wire
Grounding, 5-15R, Brown, Single Pack

Features

- Combo Duplex
- Commercial/Industrial Grade
- 15A 125V
- 2-Pole 3-Wire Grounding
- 5-15R

Application

Extra Heavy Duty Industrial Specification Grade

General

Catalog Number	BRY5292
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Series	Heavy Duty
Style	Finder Groove Face
Type	Combination Receptacle
UPC	781786005174

Dimensions

Dimensions	3.28 in x 1.54 in x 1.16 in
Display Size	Standard Sized Product
Height	1.16 in
Length	3.28 in
Weight	0.3 lb

Width 1.54 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125/250 V
Voltage Rating Description	125/250 V
Wattage	3750

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	5-15R, 6-15R
Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - BRY5292 Specification Sheet French](#)
- [Specifications - BRY5292 Specification Sheet English](#)