



Straight Blade Devices, Receptacles,
Duplex, Commercial/Industrial Grade, 20A
125V, 2-Pole 3-Wire Grounding, 5-20R,
Single Pack, Isolated Ground

By Bryant
Catalog # [BRY5362IG](#)

Straight Blade Devices, Receptacles, Duplex,
Commercial/Industrial Grade, 20A 125V, 2-Pole 3-Wire
Grounding, 5-20R, Orange, Single Pack, Isolated Ground

Features

- Duplex
- Commercial/Industrial Grade
- 20A 125V
- 2-Pole 3-Wire Grounding
- 5-20R

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

Standards - RoHS Compliance	CM
Status	
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	5-20R

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

Current

Amperage Rating	20 A
Voltage Rating Description	125 V
Current Rating	20 A
Voltage Rating	125 V
Wattage	2500
Connectivity	Back and Side Wired



Phase	Single Phase
Current / Amperage Rating	20 A

Dimensions

Length	3.28 in
Display Size	Standard Sized Product
Weight	0.2 lb.
Height	1.16 in
Width	1.54 in
Dimensions	3.28 in x 1.54 in x 1.16 in

General

Color	Orange
Style	Finder Groove Face
Series	Straight Blade
OEM Brand Name	Hubbell Bryant
UPC	781786005280
Type	Duplex Receptacle
Material - Mounting Hardware	Screw Mounting
Item Type	Traditional Duplex
Material	Composite

Logistics

Pallet Quantity	5500
Carton Quantity	10

Product Assets

- [Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Catalog Page \[English\]](#)