



Straight Blade Devices, Male Plug, Heavy Duty, Industrial/Commercial Grade, Straight, 20A 125V, 2-Pole 3-Wire Grounding, 5-20P, Yellow, Single Pack

By Bryant
Catalog # [BRY5366NPSY](#)



Straight Blade Devices, Male Plug, Heavy Duty, Industrial/Commercial Grade, Straight, 20A 125V, 2-Pole 3-Wire Grounding, 5-20P, Yellow, Single Pack

Features

- Heavy Duty
- Industrial/Commercial Grade
- Straight
- 20A 125V
- 2-Pole 3-Wire Grounding

Application

Extra Heavy Duty Industrial Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	5-20P

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

Configuration

Cord Type	All Portable
-----------	--------------

Current

Current Rating	20 A
Amperage Rating	20 A
Voltage Rating Description	125 V
Phase	Single Phase
Current / Amperage Rating	20 A

Connectivity	Screw Terminals
Wattage	2500
Voltage Rating	125 V

Dimensions

Display Size	Standard Sized
Length	2.18 in
Width	1.52 in
Weight	0.1 lb.
Height	1.38 in
Dimensions	2.18 in x 1.52 in x 1.38 in

General

Series	Industrial
OEM Brand Name	Hubbell Bryant
Cord Range	0.245"-0.655"
Style	Extra Heavy Duty
Color	Yellow
Item Type	Tech-Spec Triple Gripper
Material - Mounting Hardware	Cord Mounted
Type	Plug
Material	Composite
UPC	781786134133

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)