



Straight Blade Devices, Female Connector Body, Heavy Duty, Industrial/Commercial Grade, Straight, 20A 125V, 2-Pole 3- Wire Grounding, 5-20R

By Bryant
Catalog # [BRY5369NC](#)

Straight Blade Devices, Female Connector Body, Heavy Duty, Industrial/Commercial Grade, Straight, 20A 125V, 2-Pole 3- Wire Grounding, 5-20R, Black, Single Pack



Features

- Heavy Duty
- Industrial/Commercial Grade
- Straight
- 20A 125V
- 2-Pole 3- Wire Grounding

Application

Extra Heavy Duty Industrial Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	5-20P

Conductor

Number Of Wires	3-Wire
Number Of Conductors	3-Wire Grounding
Conductor Range	#14 AWG to #10 AWG
Number Of Poles	2-Pole

Current

Current Rating	20 A
Amperage Rating	20 A
Voltage Rating Description	125 V
Current / Amperage Rating	20 A
Connectivity	Screw Terminals
Voltage Rating	125 V

Dimensions

Display Size	Standard Sized Product
Length	2.95 in
Width	1.52 in
Weight	0.15 lb.
Height	1.38 in
Dimensions	2.95 in x 1.52 in x 1.38 in

General

Series	Industrial
Cord Range	0.300"-0.655"
Style	Extra Heavy Duty
Color	Black and White
Item Type	Tech-Spec Triple Gripper
Insulation	Insulated Body
Material - Mounting Hardware	Cord Mounted
Type	Plug
Material	Composite
UPC	781786005952

Logistics

Carton Quantity	10
Pallet Quantity	4000

Operational

Temperature Rating	<ul style="list-style-type: none"> • Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact, -25° with impact.
--------------------	---

Product Assets

[Catalog \[English\]](#)