



Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, 20A 250V, 2-Pole 3-Wire Grounding, 6- 20R, Black, Single Pack

By Bryant
Catalog # [BRY5462BLK](#)



Straight Blade Devices, Receptacles, Duplex,
Commercial/Industrial Grade, 20A 250V, 2-Pole 3-Wire
Grounding, 6-20R, Black, Single Pack

Features

- Duplex
- Commercial/Industrial Grade
- 20A 250V
- 2-Pole 3-Wire Grounding
- 6-20R

Application

Extra Heavy Duty Industrial Specification Grade

General

| | |
|------------------------------|--|
| Catalog Number | BRY5462BLK |
| EU RoHS Indicator | Yes |
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| Item Type | Traditional Duplex |
| Material - Mounting Hardware | Screw Mounting |
| Number Of Poles | 2-Pole |
| Series | Extra Heavy Duty |
| Style | Finder Groove Face |
| Type | Duplex Receptacle |
| UPC | 781786005365 |

Dimensions

| | |
|--------------|-----------------------------|
| Dimensions | 3.28 in x 1.54 in x 1.16 in |
| Display Size | Standard Sized Product |
| Height | 1.16 in |
| Length | 3.28 in |
| Weight | 0.25 lb |

Width 1.54 in

Electrical Ratings

| | |
|----------------------------|---------------------|
| Amperage Rating | 20 A |
| Connectivity | Back and Side Wired |
| Current / Amperage Rating | 20 A |
| Current Rating | 20 A |
| Phase | Single Phase |
| Voltage Rating | 250 V |
| Voltage Rating Description | 250 V |
| Wattage | 5000 |

Conductor Related

| | |
|-----------------|--------------------|
| Number Of Wires | 3-Wire |
| Wire Size | #14 AWG to #12 AWG |

Certifications And Compliance

| | |
|---------------------------------------|-------|
| Nema Rating | 6-20R |
| Standards - RoHS Compliance Status | CM |

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - BRY5462BLK Specification Sheet English](#)
- [Specifications - BRY5462BLK Specification Sheet French](#)