



Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, 20A 250V, 2-Pole 3-Wire Grounding, 6- 20R, Gray, Single Pack

By Bryant
Catalog # [BRY5462GRY](#)



Straight Blade Devices, Receptacles, Duplex,
Commercial/Industrial Grade, 20A 250V, 2-Pole 3-Wire
Grounding, 6-20R, Gray, Single Pack

Features

- Duplex
- Commercial/Industrial Grade
- 20A 250V
- 2-Pole 3-Wire Grounding
- 6-20R

Application

Extra Heavy Duty Industrial Specification Grade

General

Catalog Number	BRY5462GRY
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Series	Extra Heavy Duty
Style	Finder Groove Face
Type	Duplex Receptacle
UPC	781786005372

Dimensions

Dimensions	3.28 in x 1.54 in x 1.16 in
Display Size	Standard Sized Product
Height	1.16 in
Length	3.28 in
Weight	0.1 lb

Width 1.54 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250 V
Wattage	5000

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	6-20R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - BRY5462GRY Specification Sheet English](#)
- [Specifications - BRY5462GRY Specification Sheet French](#)