



Straight Blade Devices, Receptacles,
Duplex, Commercial/Industrial Grade, 15A
250V, 2-Pole 3-Wire Grounding, 6-15R,
Ivory, Single Pack

By Bryant
Catalog # [BRY5662I](#)

Straight Blade Devices, Receptacles, Duplex,
Commercial/Industrial Grade, 15A 250V, 2-Pole 3-Wire
Grounding, 6-15R, Ivory, Single Pack

Features

- Duplex
- Commercial/Industrial Grade
- 15A 250V
- 2-Pole 3-Wire Grounding
- 6-15R

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	6-15R

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

Current

Current Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	250 V
Phase	Single Phase
Current / Amperage Rating	15 A
Connectivity	Back and Side Wired



Wattage	3750
Voltage Rating	250 V

Dimensions

Display Size	Standard Sized Product
Length	3.28 in
Width	1.54 in
Weight	0.2 lb.
Height	1.16 in
Dimensions	3.28 in x 1.54 in x 1.16 in

General

Series	Extra Heavy Duty
OEM Brand Name	Hubbell Bryant
Style	Finder Groove Face
Color	Ivory
Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Type	Duplex Receptacle
UPC	781786005495

Logistics

Carton Quantity	10
Pallet Quantity	5500

Product Assets

- [Catalog \[English\]](#)
[Catalog Page \[English\]](#)