




## Straight Blade Devices, Watertight Series, Receptacle, Duplex, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Yellow

By Bryant  
Catalog # [BRY60W33D](#)

Straight Blade Devices, Watertight Series, Receptacle, Duplex, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Yellow



### Features

- Duplex
- 20A 125V
- 2-Pole 3-Wire Grounding
- 5-20R

### Specifications

Nema Rating 5-20R

### Conductor

Number Of Wires 3-Wire  
Number Of Poles 2-Pole

### Current

Current / Amperage Rating 20 A  
Amperage Rating 20 A  
Voltage Rating Description 125 V  
Voltage Rating 125 V

### Dimensions

Width 3.10 in  
Weight 0.3 lb.  
Height 1.63 in  
Length 4.56 in  
Dimensions 4.56 in x 3.10 in x 1.63 in

### General

Type Receptacle  
OEM Brand Name Hubbell Bryant  
UPC 781786380301  
Style Duplex Receptacle  
Color Yellow

### Product Assets

[Catalog \[English\]](#)  
[Catalog Page \[English\]](#)